

	Vaseco Helium Bubbler Box	Vaseco Hydrogen Bubbler Box	Vaseco Helium Bubbler Box
Calibrated To	1% Helium, 99% Nitrogen	5% Hydrogen, 95% Nitrogen	1% Helium, 99% Nitrogen
Nominal Leak Rate	100 scf / year	100 scf / year	Lower limit: 20 scf / year Upper limit: 100 scf / year
Temperature Coefficient	6 scf / year over -25°C to +85°C	6 scf / year over -25°C to +85°C	6 scf / year over -25°C to +85°C
Accuracy	+ / - 5 scf / year	+ / - 5 scf / year	+ / - 5 scf / year
Repeatability	+ / - 2 scf / year	+ / - 2 scf / year	+ / - 2 scf / year
Weight	0.5 kg	0.5 kg	0.5 kg
Dimensions	125 x 80 x 57 mm	125 x 80 x 57 mm	125 x 80 x 57 mm
Additional Features		Part of the Vaseco H ₂ range 	Unique PASS or FAIL calibration system Alternative gases are available upon special request e.g. 5% Helium, 95% Nitrogen

All Vaseco Bubbler Boxes are supplied with a calibration certificate traceable to National Standards.

In order to ensure absolute confidence in your equipment, we would recommend that an annual re-calibration is carried out.

Do you have any Additional Calibration Requirements?

We have a state-of-the-art calibration laboratory maintained to the highest standards that may be of interest, suitable for calibrating all standard leaks.

Contact us for more information or visit www.vaseco.com/calibration.